


## Effect RIC 10 (S-RECEIVER )

Minimal to severe hearing losses  
E7/E6/E5/E4/E3



Fitting range



Key Features	E7	E6	E5	E4	E3
Processing and fine-tuning channels	15	12	10	6	6
Experience Level Manager	•	•	•	•	•
Programs*	5	4	3	3	3
Automatic Adaptive Directionality channels	15	12	10	6	6
Volume Control II*	•	•	•	•	•
Ambient Noise Rejection II	•	•	•	•	•
Noise reduction	•	•	•	•	•
Linked ZEN	•	•	•	•	•
Linear Frequency Transposition	•	•	•	•	•
Acoustic Situation Technology	11 (IE)	7 (IE)	4	3	
Impulse Noise Rejection II	•	•	•		
Speech Enhancer	II/Linked	Linked			
Real Ear Effect	•	•			
Wind Noise Control II	•				
High-frequency boost	•				
<b>Connectivity</b>					
DEX assistive listening device compatibility	•	•	•	•	•
<b>Accessories</b>					
Acoustic remote control App	•	•	•	•	•
COM-DEX App	•	•	•	•	•

\*Via DEX or app

### Colours


069/Summer Gold, 081/Tan Silk, 118/Tech Black, 119/Silver Grey, 121/Titanium Grey, 123/Autumn Beige

**TECHNICAL DATA**


		<b>EAR SIMULATOR</b> IEC 60118-0:1983, + A1:1994	<b>2CC COUPLER</b> IEC 60118-0:2015, ANSI S3.22-2014
OSPL90	1600 Hz Peak Average	110 dB SPL 118 dB SPL 110 dB SPL	101 dB SPL 107 dB SPL 102 dB SPL
Acoustic output (Input 60 dB SPL)	1600 Hz Peak Average	94 dB SPL 102 dB SPL 89 dB SPL	85 dB SPL 91 dB SPL 85 dB SPL
Full-on gain (Input 50 dB SPL)	1600 Hz Peak Average	59 dB SPL 63 dB SPL 58 dB SPL	49 dB SPL 52 dB SPL 50 dB SPL
Acoustic Frequency range		100 Hz - 10000 Hz	100 Hz - 9300 Hz
Harmonic distortion (Input 70 dB SPL)	500 Hz 800 Hz 1600 Hz	<2% <2% <2%	<2% <2% <2%
Equivalent input noise		23 dB SPL	23 dB SPL
Battery current (stand by)		0.97 mA	0.97 mA
Battery current		0.99 mA	0.99 mA
Battery life / hours (Type 10 Zn-Air, 100 mAh)*		100 h	100 h
Mobile phone immunity (IEC 60118-13:2016, ANSI C63.19:2011)		IRIL: -40/-7/-6 dB SPL	U-rating: M4

\*Battery life in real-life situations depends among other things on the hearing aid features used, streaming time, and the quality of the battery used.


**MAXIMUM OUTPUT - EAR SIMULATOR**



**MAXIMUM OUTPUT - 2CC COUPLER**



**OUTPUT - EAR SIMULATOR**



**OUTPUT - 2CC COUPLER**

